


# HOW TO:

## Measure Silicone Edge Graphic Frames

### WHAT YOU'LL NEED

- Tape measure with both inches and millimeters
- Pen & Paper
- Camera (or use camera on phone)

### 1 MEASURE THE FRAME



Measure the **outermost dimensions** of the Silicone Edge Graphic (SEG) frame.

Use the **inches** side of the tape measure to record the width from side to side and height from top to bottom.

### 2 MEASURE THE FRAME CHANNEL



Measure the **frame channel**, the groove around the perimeter of the frame, where the silicone beading is inserted. This thickness varies depending on the frame manufacturer.

Pull a section of the graphic from the frame to access the frame channel.

Use the **millimeter** side of the tape measure held straight across the channel at any point.

Snap a photo of the channel next to the tape measure.

### 3 SEND THE DIMENSIONS



Email the outer frame dimensions (*in inches*) and a photo of the frame channel thickness (*in millimeters*).

Be sure to include your store or company name in the subject line!